



HFMED®

YD01-4LED

Emergency Cold light operating lamp


Instructions for use:

For basic health infrastructures; in support of surgical interventions in operating theatres, delivery rooms, dressing rooms and emergency departments.

After each intervention the handle should be disinfected, cleaned and sterilized by steam sterilizer.

Never touch a halogen bulb with bare hands.

Must be used and maintained properly, according manufacturer's instructions.



WHY CHOOSE US



OUR ADVANTAGE

The company keeps to the concept of being oriented by science and technology and taking quality as life. Now the company has passed the certification of ISO9001:2008, ISO13485:2003, CE and SGS.



MANAGEMENT

"Quality first, Credit first, Service first" is our tent. Huifeng are looking forward to sincere cooperation with you. Let's advance and pursue a wonderful future by mutual efforts.



SALES MARKET

all has its domestic sales amount coming out at the top and some products have ready sale in Southeast Asia. Its products can be found in all



Official QR code



HFMED®

YOUR IDEAL SUPGICAL LIGHT SUPPLIER
SHANGHAI HUIFENG MEDICAL INSTRUMENT CO., LTD.

Address: NO.885, Qiuxing Road, Nicheng Town, Pudong New Area,shanghai,China.

Tel: +86-021-58084992

Mob: +86-13918165133

Email: lisa@huifeng-co.com

web: <http://en.huifeng-co.com>

HFMED®

CE




YD01-4LED

Emergency Cold light operating lamp



HFMED

SHANGHAI HUIFENG MEDICAL INSTRUMENT CO.,LTD



YD01-4LED

Product Description

Device used for providing a specialized source of light for illumination of a site of medical intervention. It provides a high intensity, high colour rendering field of light that minimizes shadows and the emission of heat. Adjustable Operating field diameter with focus



Automatic switch from mains to batteries in case of power failure
With battery status indicator
Removable autoclavable handle
Power supply: The supplier has to supply the right voltage, plug and socket type that fit the country it is delivering the goods to. The country of destination would be stated in the UNFPA's



Mobile on heavy sturdy stand,
On 4 antistatic ball-bearing swivel castors, 2 with breaks
Spring balanced articulating arm
Low centre of gravity for optimal stability and reach



Main Technical Data

YD01-4LED	Shadowless Operating lamp
Illuminance	≥80,000
Colour temperature	4800±300K
Import power	150VA
Illuminance depth	≥500mm
Total irradiance	547W/ m ²
Size of light field	160-220mm
LED bulb life(hr)	≥50,000
Rated power of bulb	3.2V/1W(32pc led bulb)
Power supply voltage	220V/50Hz
Bulb	cold light
Accessories/ spare parts/consumables	
	1 x Set of spare halogen bulbs
	1 x Spare handle
	1 x Set of spare fuses